# 10 Liters 240W Medical Ultrasonic Cleaner SS304 For Instruments

#### **Basic Information**

Place of Origin: ChinaBrand Name: SKYMEN

• Certification: CE, RoHS, FCC, REACH

Model Number: 040S Minimum Order Quantity: 1

Price: Negotiation
Packaging Details: Carton box
Delivery Time: In Stock
Payment Terms: T/T

Supply Ability: 5000pcs per month



# **Product Specification**

Model: 040S Capacity: 10L

Certification: CE, RoHS, FCC,ISO
 Cleaning Type: Immersion / Soak
 Internal Tank Size: 300\*240\*150cm

Transducer: 4pcsUltrasonic Power: 240WHeating Power: 200W

Materials: Stainless Steel 304

• Tank Capacity: 10L

• Timer: 0-30 Minutes Adjustable

Highlight: 240W Medical Ultrasonic Cleaner,
 10 Liters Medical Ultrasonic Cleaner,

SS304 Ultrasonic Instrument Cleaner



# More Images







#### **Product Description**

Stainless Steel Tank digital bench top Ultrasonic Cleaner 10 Liter Removing Rust Grease

#### Specification:

Ultrasonic Frequency	40KHz			
Material	Stainless Steel SUS304			
Tank Capacity	10L			
Timer	1-30minutes , Digital timer			
Heater	20°C to 80°C adjustable			
Power Supply	AC 220 ~ 240V, 50 Hz			
Ultrasonic Power 240W				
Heating Power	200 W, Digital Heating			
Tank Size	300 x 240 x 150 mm ( L x W x H )			
Unit Size	380x 290x 280 mm ( L x W x H )			
Package Size	440 x 365x 360 mm ( L x W x H )			
N.W.	7.5 kg			
G.W.	8.5 kg			

#### Features:

- · Digital Control display
- More convenient for operation
- Stainless steel tank has resistance to wear and long work life.
- Tank capacity: 6.5L
- Digital timer, clear digital LCD display
- · With Stainless steel basket
- Use just tab water, or industrial solvent cleaner for more higher cleaning requirement
- Industrial control chip microcontroller.flexible circuit boards control, more secure & stable

#### Stainless Bench Top

Model	Capacity	Tank Size	Ultrasonic Power	Heating Power	Frequency
	(L)	(L*W*H)mm	(W)	(W)	(KHz)
800	0.8	150*85*65	35	0	40
009	0.9	150*135*65	60	100	40
010T	2	150*165*100	60	100	40
020S	3.2	240*135*100	120	100	40
030S	4.5	300*150*100	180	200	40
031S	6.5	300*150*150	180	200	40
040S	10	300*240*150	240	200	40
060S	15	330*300*150	360	300	40
080S	22	500*300*150	480	500	40
100S	30	500*300*200	600	500	40

Ultrasonic cleaning depends upon cavitation: The rapid formation and violent collapse of minute bubbles or cavities in a cleaning liquid. This activity creates a highly effective and unique penetrating action that blasts dirt from wherever it hides. Nothing cleans faster, safer or more thoroughly.

#### Following advantages:

- · Faster cleaning
- · Damage free cleaning
- · Increased distribution of ultrasound energy eliminating the standing waves
- · Improved cavitation
- · Facilitate the ultrasonic wave crossing through the mesh wire basket and the complicated objects to be cleaned

#### Suggested applications:

- 1. Scientific lab:Eyeglass Frames, Lab Glassware, Optical & Contact Lenses, Pipettes, Test Tubes
- 2. Electronics Manufacturing: Capacitors, Ceramic Substrates, PC Boards, Packaging Components, SMDs
- 3. Medical &Dental Labs,Burs,Blood Oxygenators,Cannulae,Dental Instruments,Syringe Parts
- 4. Jewelry Manufacturing: Chains, Charms, Coins, Intricate Settings, Precious Metals & Gemstones
- 5. In Auto Industry: Carburetor, Castings, Fuel Injectors, Machined Parts, Stamped Parts, Switches






Products details:

# **PRODUCT DETAIL**

SKYMEN specialize in ultrasonic cleaners manufacturing since 2007, Professional team, quality assurance






# Cooling vents

Quickly cool the internal components of the machine, protecting the circuit board.

2

#### Insulation handle

Insulation handle design, anti-static, anti-high temperature, not slippery hand, more secure.







Double insurance




Independent switch operation safety, built-in spare fuse, double insurance.



# SUS304 tank

Thickness 1.1mm, heat-resisting and corrosion-resisting, safety and health







#### Drain valve

The drain vavle is made of high quality stainless steel, corrosion-resistant and switch adjustable



# Non-slip pad

Non-slip anti-shock pad, place all surfaces without sliding



#### Cleaning Effect:




Before



After







The washing machine is operated by single chip software.

The cleaning machine's sound reduction cover and cleaning tank are made of high quality stainless steel.

The washing machine has good sealing performance and has sound insulation and heat insulation effect.

Digital display over temperature, over voltage, over current, low water level, no solution protection indication.

Digital memory, setting display ultrasonic working time, ultrasonic power, liquid level (and actual liquid level), heating temperature (and actual temperature).

The cleaning machine circuit has an automatic frequency sweep function, which can generate a continuous pulse jet, which makes the cleaning effect more obvious and the work is more stable.

The cleaning circuit and device are upgraded and matched, and the power conversion rate is high and the reactive power loss is low.



#### **Skymen Technology Corporation Limited**



86-755-27094405



info@skymen.cc



skymenultrasonic.com

Floor 1st & 2nd, Building 3, Tanggang Taifeng Industrial Park, Dawangshan Community, Shajing Street, Bao'an District, Shenzhen